

Safety En

Full lift safety valve with spring loading. (AIT)



EP

AP

ES

AS

Mod. 695



EP

AP

ES

AS

Mod. 895 CRYOGENIC

Connection: Male thread x Female thread
MR1 x FR2: 3/8"x1/2" to 1"x1"

Material: Bronze. PMS-36 bar
 Stainless steel. PN-40

Seal: PTFE (Teflon)
 Silicone's rubber
 Fluoroelastomer (Viton)
 Perfluoroelastomer (FFKM)

The valve works as an automatic pressure releasing regulator activated by the static pressure existing at the entrance to the valve and is characterized by its ability to open instantly and totally.

Design in accordance with "International Standard ISO 4126-1 Safety Valves".

Depending on version



-60°C to +200°C



0,20 bar to 36,00 bar



Steam/Gases/Liquids

Connection: Male thread x Female thread

MR1 x FR2: 3/8"x1/2" to 1"x1"

Material: Bronze. PMS-36 bar
 Stainless steel. PN-40

Seal: PTFE (Teflon)

The valve works as an automatic pressure releasing regulator activated by the static pressure existing at the entrance to the valve and is characterized by its ability to open instantly and totally.

Design in accordance with "International Standard ISO 4126-1 Safety Valves".

Depending on version



-196°C to +60°C



0,20 bar to 36,00 bar



Steam/Gases/Liquids